



your
hearing
network

AARP

Wireless Inium Sense Custom Product Order Form



YHN Order Confirmation # (required when sending impressions):

Impressions on file? yes no Order Date:

| Your Information | Ship To Information | | | | Fitter's information | | | |
|-------------------|---------------------|--|-------------------------|--|----------------------|--|------------------|--|
| | HearUSA PO # | | | | Today's Date: | | Fitting Date: | |
| | Phone #: | | Bill To Number: 4001287 | | Fitter's Name: | | Fitter's E-mail: | |
| | Company Name: | | | | Patient Information | | | |
| | Address 1: | | | | First Name: | | Middle Init: | |
| | Address 2: | | | | Last Name: | | Age: | |
| City: State: Zip: | | | | | | | | |

| Wireless Instrument | Select Model: | Alta2 Pro | | Alta2 | | Nera2 Pro | | Nera2 | | Ria2 Pro | | Ria2 | | ITE Combination Controls for ITC 312, HS, FS or Ultra Power offers only 1 volume wheel (loudness) and 1 push button (program) for each binaural fitting. Select one option for each instrument desired. Volume Wheel L R Push Button L R | | | | | | | | | | | | | | | | | | | | | |
|----------------------|---------------|--|------------|------------------------|-----------------|-----------|-----------------------------------|--------|--------|--------------------|--------------------------|------|----------|---|----------------------|--|--|--|--|--|--|---------------|-------|-------|------------|---------------|-----------------|--|-----------------|--|--|--|--|--|--|
| | | Battery | | Omni Only [†] | PB* | VW* | Auto Phone (not avail. w/ T-coil) | T-coil | Auto-T | Power [†] | Ultra Power [†] | | | | | | | | | | | | | | | | | | | | | | | | |
| | | L | R | L | R | L | R | L | R | L | R | L | R | | | | | | | | | | | | | | | | | | | | | | |
| CIC | 10 | | | STD | | | NA | NA | NA | NA | | | NA | | | | | | | | | | | | | | | | | | | | | | |
| ITC | 312 10 | | | STD | | | NA | NA | NA | NA | | | NA NA | | | | | | | | | | | | | | | | | | | | | | |
| Half Shell | 312 13 | | | NA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Full Shell | 312 13 | | | NA | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| IIC - Alta2 Pro | 10 | <table border="1"> <thead> <tr> <th colspan="7">ConnectLine™ Options</th> </tr> </thead> <tbody> <tr> <td>Streamer Pro:</td> <td>Black</td> <td>White</td> <td>TV Adaptor</td> <td>Phone Adaptor</td> <td>ConnectLine Mic</td> <td></td> </tr> <tr> <td>Remote Control:</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> </tbody> </table> | | | | | | | | | | | | | ConnectLine™ Options | | | | | | | Streamer Pro: | Black | White | TV Adaptor | Phone Adaptor | ConnectLine Mic | | Remote Control: | | | | | | |
| ConnectLine™ Options | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Streamer Pro: | Black | White | TV Adaptor | Phone Adaptor | ConnectLine Mic | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| Remote Control: | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| IIC - Nera2 Pro | 10 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| IIC - Ria2 Pro | 10 | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |

* ** Please see next page for technical information

| Color / Options | Faceplate/Shell Color | | | | | |
|---|---|-------------------------|-----------------|--|-----------|--|
| | Pink 01 (default) | | | IIC Colors: | | |
| | Tan 02 | | | Shell: Red/Blue (default) | | |
| | Medium Brown 03 faceplate / clear shell | | | Faceplate: Black (default) | | |
| | Dark Brown 04 faceplate / clear shell | | | Clear Shell (specify faceplate color) | | |
| | Clear Shell (specify faceplate color) | | | (pink, tan, medium brown, dark brown or black) | | |
| Options | | | | | | |
| Canal Length: (Factory STD unless otherwise marked) | | | | | | |
| Medium | Long | As marked on impression | | | | |
| Other Options | | | | | | |
| Canal Lock | Raised VW | Raised PB | Removal String | | | |
| Spanish Instructions | Clothing Loop | | Removal Notches | | | |
| Venting: Vents are based on the calculation in Genie unless otherwise selected. | | | | | | |
| Pressure vent | 1.0mm | 1.4mm | 2.4mm | 3.0mm | Free vent | |

| Audiometric Information (Required) | | | | | | | |
|------------------------------------|-----|-----|----|----|----|----|----|
| Hz | 250 | 500 | 1K | 2K | 3K | 4K | 6K |
| AC L | | | | | | | |
| AC R | | | | | | | |

Return Impressions
OK to make non-wireless for smaller size
Substitutions may be made without calling

Please Send:
New Flex Strips New Cables Shipping Bags
Custom Product Forms RITE Mold Forms
Impression Boxes Airbills Service Forms

Special Instructions:

Internal use only
Do not write

Submit this form to orders@YourHearingNetwork.com or fax to 866-713-8258.



Visit www.pro.oticonusa.com for more product information

Venting

All vents are calculated in Genie, unless otherwise indicated on the order form. For a specific vent type please note it in special instructions.



Collection Vent

Cone shape channel, round opening faceplate, "D" opening on canal tip. Most common for ITC, HS, and FS where pressure vents not necessary.



Cast Vent

Straight channel through device. Round opening on faceplate and canal tip. Used when pressure vents are indicated.



Oval Vent

Oval openings used for smaller instruments IIC and CIC.



Free Vent

Free form openings, takes advantage of space to ensure largest vent possible.

Accessories



T-Cap

The nano-coated, waxrepellent T-Cap filter is used for all miniature custom styles.



O-Cap

The new nano-coated O-Cap microphone protection filter is designed to reject wax and fits all instruments using battery size 312 and 13.



ProWax

Providing advanced receiver port protection, the ProWax filter fits all styles in the new Oticon custom program.



T Cap (mic cover)

Gray compact/Black tools
Part Number (1 pc):
123328 - Beige
123330 - Light Brown
123331 - Med Brown
123329 - Dark Brown
123327 - Black



O Cap (mic cover)

Gray compact/Black tools
Part Number (1 pc):
128003 - Beige
128004 - Light Brown
128005 - Med Brown
128006 - Dark Brown



ProWax

Gray "turtle"/Lt Gray tools
Part Number (1 pc):
123367

Custom Option for Special Needs

| | | | | | | |
|-----------------------------------|------------------------------|--|---------------------------|--|------------------------------------|--|
| Instrument Removal Options | Large Ball | | Reinforced Removal Line | | Door Hook | |
| Tactile Options | Raised Push Button | | VW Large, Small or Raised | | Battery Indicator | |
| Clothing Loops | Loops: Metal Small and Large | | Plastic: Small and Large | | Plastic Combo: Loop+removal string | |
| Retention Options | Canal lock | | Helix Lock | | Spiral Retention Ring | |

Please include your request on the comment line of the order form. Options available space permitting and may not be available on all models.

* Push Button and VC configuration. Please select only 1 option per device.

† All models default to Directional Microphones unless Omni is selected.

‡ Technical information re 2cc coupler: Power Receiver: OSPL90 PK 121, PK Gain: 54, Ultra Power Receiver: OSPL90 PK 127, Pk Gain: 62