



YHN Order Confirmation # (required when sending impressions):

Order Date:

Your Information		Ship To Information		Fitter's information	
Your Information	HearUSA PO #	Bill To Number: 4001287		Today's Date:	Fitting Date:
	Phone #:			Fitter's Name:	
	Company Name:			Fitter's E-mail:	
	Address 1:			Patient Information	
	Address 2:			First Name:	Middle Init:
City:	State:	Zip:	Last Name:	Age:	

Wireless Instrument	Select Model:	Alta2 Pro	Alta2	Nera2 Pro	Nera2	Ria2 Pro	Ria2	ITE Combination Controls for ITC 312, HS, FS or Ultra Power offers only 1 volume wheel (loudness) and 1 push button (program) for each binaural fitting.  Select one option for each instrument desired.  Volume Wheel      L      R Push Button      L      R			
		Battery	Omni Only <sup>†</sup>	PB*	VW*	Auto Phone (not avail. w/ T-coil)	T-coil		Auto-T	Power <sup>†</sup>	Ultra Power <sup>†</sup>
		L R	L R	L R	L R	L R	L R		L R	L R	L R
CIC	10		STD		NA	NA	NA	NA		NA	
ITC	312 10		STD		NA	NA	NA	NA		NA NA	
Half Shell	312 13		NA								
Full Shell	312 13		NA								
IIC - Alta2 Pro	10		<b>ConnectLine™ Options</b> <b>Streamer Pro:</b> Black      White      TV Adaptor      Phone Adaptor      ConnectLine Mic <b>Remote Control:</b>								
IIC - Nera2 Pro	10										
IIC - Ria2 Pro	10										

\* \*\* Please see next page for technical information

Color / Options	Faceplate/Shell Color	
	Pink 01 (default)	<b>IIC Colors:</b>
	Tan 02	Shell: Red/Blue (default)
	Medium Brown 03 faceplate / clear shell	Faceplate: Black (default)
	Dark Brown 04 faceplate / clear shell	Clear Shell (specify faceplate color)
Clear Shell (specify faceplate color)	(pink, tan, medium brown, dark brown or black)	
Options		
Canal Length: (Factory STD unless otherwise marked)		
Medium	Long      As marked on impression	
Other Options		
Canal Lock	Raised VW      Raised PB      Removal String	
Spanish Instructions	Clothing Loop      Removal Notches	
Venting: Vents are based on the calculation in Genie unless otherwise selected.		
Pressure vent	1.0mm      1.4mm      2.4mm      3.0mm      Free vent	

Audiometric Information (Required)							
Hz	250	500	1K	2K	3K	4K	6K
AC L							
AC R							

Return Impressions  
 OK to make non-wireless for smaller size  
 Substitutions may be made without calling

Please Send:  
 New Flex Strips      New Cables      Shipping Bags  
 Custom Product Forms      RITE Mold Forms  
 Impression Boxes      Airbills      Service Forms

Special Instructions:

Internal use only  
Do not write

Venting

All vents are calculated in Genie, unless otherwise indicated on the order form. For a specific vent type please note it in special instructions.



**Collection Vent**

Cone shape channel, round opening faceplate, "D" opening on canal tip. Most common for ITC, HS, and FS where pressure vents not necessary.



**Cast Vent**

Straight channel through device. Round opening on faceplate and canal tip. Used when pressure vents are indicated.



**Oval Vent**

Oval openings used for smaller instruments IIC and CIC.



**Free Vent**

Free form openings, takes advantage of space to ensure largest vent possible.

Accessories



**T-Cap**

The nano-coated, waxrepellent T-Cap filter is used for all miniature custom styles.



**O-Cap**

The new nano-coated O-Cap microphone protection filter is designed to reject wax and fits all instruments using battery size 312 and 13.



**ProWax**

Providing advanced receiver port protection, the ProWax filter fits all styles in the new Oticon custom program.



**T Cap (mic cover)**

Gray compact/Black tools  
Part Number (1 pc):  
123328 - Beige  
123330 - Light Brown  
123331 - Med Brown  
123329 - Dark Brown  
123327 - Black



**O Cap (mic cover)**

Gray compact/Black tools  
Part Number (1 pc):  
128003 - Beige  
128004 - Light Brown  
128005 - Med Brown  
128006 - Dark Brown



**ProWax**

Gray "turtle"/Lt Gray tools  
Part Number (1 pc):  
123367

Custom Option for Special Needs

Instrument Removal Options	Large Ball		Reinforced Removal Line		Door Hook		
	Tactile Options	Raised Push Button		VW Large, Small or Raised		Battery Indicator	
	Clothing Loops	Loops: Metal Small and Large		Plastic: Small and Large		Plastic Combo: Loop+removal string	
	Retention Options	Canal lock		Helix Lock		Spiral Retention Ring	

Please include your request on the comment line of the order form. Options available space permitting and may not be available on all models.

\* Push Button and VC configuration. Please select only 1 option per device.

† All models default to Directional Microphones unless Omni is selected.

‡ Technical information re 2cc coupler: Power Receiver: OSPL90 PK 121, PK Gain: 54, Ultra Power Receiver: OSPL90 PK 127, Pk Gain: 62